

# Power and performance

## ReSound LiNX 3D™ 312 RIE Rechargeable



ReSound LiNX 3D Rechargeable has all of the features of ReSound LiNX 3D including superior sound quality with Binaural Directionality III along with ZPower®, a rechargeable battery with all day power.

What's more, patients will still be able to personalize their hearing experience with the ReSound Smart 3D™ app and have the benefit of direct streaming capabilities with Made for iPhone® connectivity.

### Key Product Features

#### HOURS OF POWER

ReSound LiNX 3D Rechargeable hearing aids deliver continuous, uninterrupted power up to 16 hours with no streaming. They will last up to 14 hours with 2 hours of direct streaming.

#### WORN LIKE ANY OTHER HEARING AID

Your patients won't notice the difference from a traditional hearing aid and they won't have to worry about running out of power in the middle of the day.

#### 1+ YEAR BATTERY LIFESPAN

At the end the battery's lifespan, they are changed in your office as simply and easily as a standard Zinc-Air battery.

#### CHARGES JUST LIKE A SMARTPHONE

A custom fit battery door allows the battery to be recharged without being removed so patients can place the entire hearing aid on the stand where it will be fully charged in just 4 hours.



Each order of the ZPower Rechargeable Kit comes with everything you need. Simply replace the battery door with the ZPower battery door following the instructions included in the kit. Each kit includes two battery doors, two rechargeable batteries and a charger base.

### LiNX 3D Rechargeable Color Options



ReSound GN

# Tech specs

Model	LT961-DRWZ	LT761-DRWZ	LT561-DRWZ
<b>DEVICE CONFIGURATIONS</b>			
Battery Size	Silver-zinc 312		
Receiver Power levels	LP, MP, HP & UP		
<b>AUDIOLOGICAL FEATURES</b>			
WARP compression - number of channels	17	14	12
Binaural Directionality III	●		
Spatial Sense	●		
Binaural Directionality		●	
Directional Mix Processor	●	●	●
Adjustable Directional Mix	●		
Natural Directionality II			●
Synchronized Softswitching	●	●	
Softswitching			●
Autoscope Adaptive Directionality	●		
Multiscope Adaptive Directionality		●	
Adaptive Directionality			●
Binaural Environmental Optimizer II	●		
Environmental Optimizer		●	
NoiseTracker II	●	⊙	○
Expansion	●	⊙	○
Windguard	●	⊙	○
Sound Shaper	●	●	●
DFS Ultra II	●	●	●
Music Mode	●	●	●
Auto DFS	●	●	●
Synchronized Acceptance Manager	●	●	●
Low Frequency Boost (JP receiver only)	●	⊙	⊙
Amplification strategy (WDRC/Semilinear/ Linear - UP receiver only)	●	⊙	○
Tinnitus Sound Generator with Nature Sounds	●	●	●
<b>FUNCTIONAL FEATURES</b>			
Synchronized push button*	●	●	●
SmartStart	●	●	●
PhoneNow	●	●	●
Comfort Phone	●	●	●
Ear-to-Ear communication	●	●	●
Direct audio streaming (Made for iPhone)	●	●	●
ReSound TV Streamer 2, Remote Control 2, Phone Clip+, Micro Mic, Multi Mic	●	●	●
ReSound Control app (Phone Clip+ required)	●	●	●
ReSound Smart 3D™ app	●	●	●
<b>RESOUND ASSIST</b>			
Remote Fine Tuning	●	●	●
Remote Firmware Updates	●	●	●
<b>FITTING FEATURES</b>			
Fitting Software Smart Fit 1.1 or higher	●	●	●
Fully Flexible Programs	4	4	4
Auto DFS	●	●	●
Onboard Analyzer II	●	●	●
Wireless Fitting with Airlink2/ Noahlink Wireless	●	●	●

- Ultimate
- ⊙ Advanced
- Basic

\*Also including functionality for synchronized Push Button Volume Control

## Manufacturer according to FDA:

### RESOUND NORTH AMERICA

8001 E. Bloomington Freeway  
Bloomington, MN 55420  
1.800.248.4327  
resoundpro.com

### RESOUND GOVERNMENT SERVICES

8001 E. Bloomington Freeway  
Bloomington, MN 55420  
1.800.392.9932  
resound.com/governmentservices

## Manufacturer according to Health Canada:

### RESOUND CANADA

303 Supertest Road  
Toronto, Ontario M3J 2M4  
1.888.737.6863  
resoundpro.com

